



Convertible pH Sensor, 3/4" combination pH electrode, PPS

Termékszám:	PC1R1A
HUF Ár (nettó):	Elérhetőségünk
Elérhető	

Analog pH sensor, can be used as a flow-through or built-in immersion probe. Suitable for highly aggressive processes requiring more frequent replacement. Without in-built temperature element.

PPS, convertible body style, 4.5 m analog cable, general purpose glass pH electrode, PT1000 temperature compensation

Low Price-Great Performance

These combination sensors are designed for specialty applications for immersion or in-line mounting. The reference cell features a double-junction design for extended service life, and a built-in solution ground. The body is molded from chemically-resistant PPS or PVDF, and the reference junction is coaxial porous PTFE. All sensors are rated 0 to 105°C up to 100 psig, and have integral 4.5 m (15 ft.) cables with tinned leads. The PC-series (for pH) and RCseries (for ORP) combination sensors are ideal for measuring mild and aggressive media.

Special Electrode Configurations

Sensors with rugged dome electrodes, "easy-to-clean" flat glass electrodes, and even HF (hydrofluoric acid) resistant glass electrodes are available for a wide variety of process solutions.

Temperature Compensation Element Option

The PC-series combination pH sensors are available with or without a PT1000 ohm RTD temperature element. The RC-series combination ORP sensors are supplied without a temperature element.

Versatile Mounting Styles

Sensors are available in three mounting styles—convertible, insertion, and sanitary.

Full-Featured "Plug and Play" Hach Digital SC Controllers

There are no complicated wiring or set up procedures with any Hach SC controller. Just plug in any combination of Hach digital sensors and it's ready to use—it's "plug and play." One or multiple sensors-the SC controller family allows you to receive data from up to eight Hach digital sensors in any combination using a single controller.

Műszaki adatok

Anyag:	General purpose
Anyaga:	PPS, General Purpose
Áramlás:	0 - 2 m/s
Átviteli távolság:	Max. 100 m when used with the Hach digital gateway and SC1000 controller
Garancia:	6 hónap
Hőmérséklet kompenzáció:	Yes, PT1000
Kábel hossz:	4.5 m terminated with stripped and tinned wires
Méréstartomány:	0 - 14 pH
Működési hőmérséklet tartomány:	0 - 105 °C

Nyomástartomány:	6,9 bar 100 °C-on
Paraméter:	pH
Precizitás (RDS):	± 0.1 pH under reference conditions
Szondatípus:	Convertible